

# 71420FR Cut Sheet



Bryant industrial heavy duty single locking blade receptacle, 20A, 125/250 VAC, 1-phase, 3-pole, 4-wire, NEMA L14-20, nylon molded housing, black.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/71420FR>

## Technical Specifications

|                 |                       |
|-----------------|-----------------------|
| Brand           | Bryant                |
| Item            | Receptacle            |
| Application     | Industrial heavy duty |
| Receptacle Type | Single                |
| Blade Type      | Locking               |
| With Cap        | No                    |
| Self-grounding  | No                    |
| Amperage Rating | 20A                   |
| Voltage Rating  | 125/250 VAC           |

|                  |                            |
|------------------|----------------------------|
| Number of Phases | 1                          |
| Number of Poles  | 3                          |
| Number of Wires  | 4                          |
| Wire Size        | 14-8 AWG solid or stranded |
| Copper Wire Only | Yes                        |
| Configuration    | NEMA L14-20                |
| Housing Material | Nylon molded               |
| Color            | Black                      |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | E2258                                  |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | 016215                                 |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/71420FR.pdf>  
See store item page for other formats.