

# 71620NP Cut Sheet



Bryant industrial heavy duty locking blade plug, 20A, 480 VAC, 3-phase, 3-pole, 4-wire, NEMA L16-20, accepts cord size 0.46-1.15in, nylon housing, black and white.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/71620NP>

## Technical Specifications

<b>Brand</b>	Bryant
<b>Item</b>	Plug
<b>Application</b>	Industrial heavy duty
<b>Blade Type</b>	Locking
<b>With Cap</b>	No
<b>Self-grounding</b>	No
<b>Amperage Rating</b>	20A
<b>Voltage Rating</b>	480 VAC
<b>Number of Phases</b>	3

<b>Number of Poles</b>	3
<b>Number of Wires</b>	4
<b>Wire Size</b>	18-8 AWG
<b>Copper Wire Only</b>	No
<b>Configuration</b>	NEMA L16-20
<b>Cord Diameter</b>	0.46-1.15in
<b>Housing Material</b>	Nylon
<b>Color</b>	Black and white

## Agency Approvals

<b>UL Listed File #</b>	E1381
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	016215
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/71620NP.pdf>  
See store item page for other formats.