

71630FR Cut Sheet



Bryant industrial heavy duty single locking blade receptacle, 30A, 480 VAC, 3-phase, 3-pole, 4-wire, NEMA L16-30, nylon molded housing, black.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/71630FR>

Technical Specifications

Brand	Bryant
Item	Receptacle
Application	Industrial heavy duty
Receptacle Type	Single
Blade Type	Locking
With Cap	No
Self-grounding	No
Amperage Rating	30A
Voltage Rating	480 VAC
Number of Phases	3
Number of Poles	3
Number of Wires	4
Wire Size	14-8 AWG solid or stranded
Copper Wire Only	Yes
Configuration	NEMA L16-30
Housing Material	Nylon molded
Color	Black

Agency Approvals

UL Listed File #	E2258
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	016215
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document