

72230NC Cut Sheet



Bryant industrial heavy duty locking blade connector, 30A, 277/480 VAC, 3-phase, 4-pole, 5-wire, NEMA L22-30, accepts cord size 0.46-1.15in, nylon housing, black and white.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/72230NC>

Technical Specifications

Brand	Bryant
Item	Connector
Application	Industrial heavy duty
Blade Type	Locking
With Cap	No
Self-grounding	No
Amperage Rating	30A
Voltage Rating	277/480 VAC
Number of Phases	3

Number of Poles	4
Number of Wires	5
Wire Size	18-8 AWG
Copper Wire Only	No
Configuration	NEMA L22-30
Cord Diameter	0.46-1.15in
Housing Material	Nylon
Color	Black and white

Agency Approvals

UL Listed File #	E1381
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	016215
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/72230NC.pdf>
See store item page for other formats.