7231-29541-0000000 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



Murrelektronik field wireable solenoid valve connector, 18mm DIN 43650 Form A molded connector, 45-degree cable entry, 24–230 VAC/VDC, 18–14 AWG, accepts cable diameter size 0.19–0.37in, IP65, bridge rectifier protection, LED indication.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/7231-29541-0000000

Technical Specifications

Brand	Murrelektronik
Item	Field wireable solenoid valve connector
Connector Type	18mm DIN 43650 Form A molded connector
Cable Entry	45-degree
Voltage Rating	24–230 VAC/VDC
Conductor Size	18–14 AWG
Cable Diameter Size	0.19–0.37in
IP Rating	IP65
Protection Type(s)	bridge rectifier
Indicating Type	LED indication

Agency Approvals

CE	View CE declarations
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com
/static/drawings/2d/7231-29541-0000000.pdf
See store item page for other formats.