

7310SB Cut Sheet



Greenlee Slug-Buster knockout punch set, 15 pieces, 0-degree fixed head, round, 1/2in conduit-4in conduit, plastic case.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7310SB>

Technical Specifications

Brand	Greenlee
Series	Slug-Buster
Item	Knockout punch set
Number of Pieces	15
Knockout Size	1/2in conduit-4in conduit
Punch Shape	Round
Bolt Size	7/16in, 3/4in and 1-1/8in
Head Type	0-degree fixed
Maximum Punch Thickness	10ga mild steel

Operation Type	Manual hand pump
Application	Hole cutting
For Use On	Steel, plastic, stainless steel and non-ferrous metals
Set Includes	Includes (10) Conduit Slug-Buster punch & die (1/2in, 3/4in, 1in, 1-1/4in, 1-1/2in, 2in, 2-1/2in, 3in, 3-1/2in, 4in), (3) hydraulic draw bolt (7/16in, 3/4in, 1-1/8in), (1) 746A ram w/ 767 manual hand pump & hose and (1) plastic case
Package Type	Plastic case

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document