

732-0001 Cut Sheet



Trumeter electromechanical hour meter, 3.6mm 6-digit analog, 10-80 VDC input, round 3-hole mount, 1/4in (6.4mm) spade terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/732-0001>

Technical Specifications

Brand	Trumeter
Item	Hour meter
Counter Type	Electromechanical
Count Direction	Up
Display Type	Analog
Display Size	3.6mm 6-digit
Display Units	Hours and tenths
Input Signal	10-80 VDC

Operating Voltage	10-80 VDC
Mounting	Panel
Mounting Type	Round 3-hole mount
Mounting Hole Size	2.0in diameter
Connector Type	1/4in (6.4mm) spade terminals
Additional Information	NEMA 4/4X compliant from the front when using the optional gasket

Agency Approvals

UL Listed File #	None
UL Recognized File #	E123666
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/732-0001.pdf>
See store item page for other formats.