

73894 Cut Sheet

Viking combination drill bit and machine tap, 1/4-20 UNF, 1/4in hex, high-speed steel (HSS), gold oxide finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/73894>

Technical Specifications

Brand	Viking
Item	Combination drill bit and machine tap
Thread	1/4-20 UNF
Thread Length	0.33in
Number of Flutes	2
Flute Style	Spiral flute
Overall Length	2.6in (66mm)

Tap Drill Size	Wire number size 7
Shank	1/4in hex
Material	High-speed steel (HSS)
Finish	Gold oxide
For Use On	Stainless steel, iron and steel
Application	Hole cutting and thread making

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement