

73990 Cut Sheet



Viking combination drill bit and machine tap set, 7 pieces, high-speed steel (HSS), 3-flat shank, UNC thread type, imperial, gold oxide finish, pouch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/73990>

Technical Specifications

Brand	Viking
Item	Combination drill bit and machine tap set
Number of Pieces	7
Material	High-speed steel (HSS)
Thread Type	UNC
Thread	#8-32 UNC, #10-24 UNC, 1/4-20 UNC, 5/16-18 UNC, 3/8-16 UNC, 7/16-14 UNC and 1/2-13 UNC
Drill Bit Size	Wire number size 29, wire number size 25, wire number size 7, letter size F, 5/16in, letter size U and 27/64in
Finish	Gold oxide

Point Cut	Split
Shank Type	3-flat
Application	Thread making and hole cutting
For Use On	Stainless steel, iron and steel
Measurement Type	Imperial
Package Type	Pouch
Set Includes	Includes (7) combination drill bit and machine taps (#8-32 UNC, #10-24 UNC, 1/4-20 UNC, 5/16-18 UNC, 3/8-16 UNC, 7/16-14 UNC, 1/2-13 UNC), pouch

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement