

# 73991 Cut Sheet



Viking combination drill bit and machine tap set, 7 pieces, high-speed steel (HSS), 3-flat shank, UNF thread type, imperial, gold oxide finish, pouch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/73991>

## Technical Specifications

<b>Brand</b>	Viking
<b>Item</b>	Combination drill bit and machine tap set
<b>Number of Pieces</b>	7
<b>Material</b>	High-speed steel (HSS)
<b>Thread Type</b>	UNF
<b>Thread</b>	#8-36 UNF, #10-32 UNF, 1/4-28 UNF, 5/16-24 UNF, 3/8-24 UNF, 7/16-20 UNF and 1/2-20 UNF
<b>Drill Bit Size</b>	Wire number size 29, wire number size 21, wire number size 3, letter size I, letter size Q, 25/64in and 29/64in
<b>Finish</b>	Gold oxide

<b>Point Cut</b>	Split
<b>Shank Type</b>	3-flat
<b>Application</b>	Thread making and hole cutting
<b>For Use On</b>	Stainless steel, iron and steel
<b>Measurement Type</b>	Imperial
<b>Package Type</b>	Pouch
<b>Set Includes</b>	Includes (7) combination drill bit and machine taps (#8-36 UNF, #10-32 UNF, 1/4-28 UNF, 5/16-24 UNF, 3/8-24 UNF, 7/16-20 UNF, 1/2-20 UNF), pouch

## Agency Approvals

<b>UL Listed File #</b>	N/A
<b>UL Recognized File #</b>	N/A
<b>UL Hazardous File #</b>	N/A
<b>CE</b>	None
<b>CSA File #</b>	N/A
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>