

7401160SBA Cut Sheet

KNIPEX diagonal cutters, 6.3in (159mm) overall length, induction hardened beveled cutting edges, plastic coated handles.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7401160SBA>

Technical Specifications

Brand	KNIPEX
Item	Cutters
Pliers Type	Diagonal
Overall Length	6.3in (159mm)
Insulated	No
Cutting	Induction hardened beveled cutting edges
Capacity	9/64in medium wire, 3/32in hard wire or 5/64in piano wire
Handle Type	Plastic coated handles
Application	Wire cutting
Material	Chrome vanadium heavy-duty steel, forged, oil-hardened
Applicable Standards	DIN ISO 5749

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document