

# 7401250SBA Cut Sheet

KNIPEX diagonal cutters, 10.0in (254mm) overall length, induction hardened beveled cutting edges, plastic coated handles.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7401250SBA>

---

## Technical Specifications

<b>Brand</b>	KNIPEX
<b>Item</b>	Cutters
<b>Pliers Type</b>	Diagonal
<b>Overall Length</b>	10.0in (254mm)
<b>Insulated</b>	No
<b>Cutting</b>	Induction hardened beveled cutting edges
<b>Capacity</b>	3/16in medium wire, 9/64in hard wire or 1/8in piano wire
<b>Handle Type</b>	Plastic coated handles
<b>Application</b>	Wire cutting
<b>Material</b>	Chrome vanadium heavy-duty steel, forged, oil-hardened
<b>Applicable Standards</b>	DIN ISO 5749

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>