

74020012 Cut Sheet

GAM helical rack, Module 1.5, 200 tooth, 1m length. For use with Module 1.5 pinions.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/74020012>

Technical Specifications

Brand	GAM
Item	Rack
Tooth Profile	Helical
Pressure Angle	20 degrees
Module	1.5
Number of Teeth	200
Length	1m
Material	1045 carbon steel
Hardness	50 - 55 HRC
Finish	Milled
Tooth Thickness Tolerance	-124 µm
Single Pitch Error	37 µm or less
Total Pitch Error	148 µm or less
Precision Grade	ISO Q10
For Use With	Module 1.5 pinions

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document