

7408250SBA Cut Sheet

KNIPEX high leverage diagonal cutters, 10in overall length, 1000V insulation rating, beveled cutting edges, multi-component comfort grip handles.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7408250SBA>

Technical Specifications

| | |
|--------------------------|--------------------------------------|
| Brand | KNIPEX |
| Item | High leverage diagonal cutters |
| Ratcheting | No |
| Insulation Rating | 1000V |
| Cutting | Beveled cutting edges |
| Cable Capacity | 5 AWG medium hard wire |
| Overall Length | 10in |
| Handle Type | Multi-component comfort grip handles |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |