

# 7511HV Cut Sheet



Trumeter electrical hour meter, 9mm 8-digit LCD, 5-110 VDC or 10-240 VAC input, remote, manual or disabled reset, rectangular flush mount with clip, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7511HV>

## Technical Specifications

<b>Brand</b>	Trumeter
<b>Item</b>	Hour meter
<b>Counter Type</b>	Electrical
<b>Count Direction</b>	Up/down
<b>Display Type</b>	LCD
<b>Display Size</b>	9mm 8-digit
<b>Display Units</b>	Seconds, minutes and seconds, hours and hundredths and hours and minutes
<b>Reset</b>	Remote, manual or disabled
<b>Input</b>	5-110 VDC or 10-240 VAC
<b>Mounting</b>	Panel
<b>Mounting Type</b>	Rectangular flush mount with clip
<b>Mounting Hole Size</b>	1/32 DIN
<b>Connector Type</b>	Screw terminals
<b>Includes</b>	NEMA 4X gasket
<b>Additional Information</b>	5-30 VDC externally powered backlight, requires separate resistor above 5 VDC
<b>Dangerous Goods</b>	<ul style="list-style-type: none"><li>• Battery Installed: Yes</li><li>• Packaging Instructions: 970</li><li>• UN Number: UN3091</li><li>• Hazard Type: Lithium Battery</li><li>• Battery Type: Other</li><li>• Generic Battery: CR2477</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E36690
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>