

7511 Cut Sheet



Trumeter electrical hour meter, 9mm 8-digit LCD, discrete input, remote, manual or disabled reset, rectangular flush mount with clip, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7511>

Technical Specifications

Brand	Trumeter
Item	Hour meter
Counter Type	Electrical
Count Direction	Up/down
Display Type	LCD
Display Size	9mm 8-digit
Display Units	Seconds, minutes and seconds, hours and hundredths and hours and minutes
Reset	Remote, manual or disabled
Input	Discrete
Mounting	Panel
Mounting Type	Rectangular flush mount with clip
Mounting Hole Size	1/32 DIN
Connector Type	Screw terminals
Includes	NEMA 4X gasket
Additional Information	5-30 VDC externally powered backlight, requires separate resistor above 5 VDC
Dangerous Goods	<ul style="list-style-type: none">• Battery Installed: Yes• Packaging Instructions: 970• UN Number: UN3091• Hazard Type: Lithium Battery• Battery Type: Other• Generic Battery: CR2477

Agency Approvals

UL Listed File #	None
UL Recognized File #	E36690
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document