


76249850 Cut Sheet



WIKA 111.25DW mechanical pressure gauge, 4.5in diameter, 0–100 psig, stainless steel dry case, lead-free brass wetted parts, 1/4in male NPT process connection, lower mount, NSF/ANSI 61 and NSF 372.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/76249850>

Technical Specifications

Brand	WIK A
Item	Mechanical pressure gauge
Series	111.25DW
Media Type	Potable water
Diameter	4.5in
Scale	0–100 psig
Case Type	Stainless steel dry
Wetted Parts	Lead-free brass
Process Connection	1/4in male NPT
Mounting	Lower
Potable Water Certifications	NSF/ANSI 61 and NSF 372

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document
Other	NSF Listing

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/76249850.pdf>
See store item page for other formats.