

# 76250396 Cut Sheet



WIKA manual isolation and throttling needle valve, straight body hard seat, single handle, 316L stainless steel body, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/76250396>

## Technical Specifications

|                     |                                 |
|---------------------|---------------------------------|
| Brand               | WIKAI                           |
| Item                | Needle valve                    |
| Valve Type          | Manual isolation and throttling |
| Form Factor         | Straight body hard seat         |
| Media Type          | Potable water                   |
| Operator Type       | Single handle                   |
| Body Material       | 316L stainless steel            |
| Inlet Port          | 1/4in female NPT                |
| Outlet Port         | 1/4in female NPT                |
| Minimum Temperature | 10,000 psi @ -67 °F             |
| Maximum Temperature | 4,000 psi @ 400 °F              |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |
| Other                | NSF Listing                            |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/76250396.pdf>  
See store item page for other formats.