

76250398 Cut Sheet



WIKa manual isolation and throttling needle valve, straight body hard seat, single handle, 316L stainless steel body, 1/4in male NPT inlet(s), 1/4in female NPT outlet(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/76250398>

Technical Specifications

| | |
|----------------------------|---------------------------------|
| Brand | WIKa |
| Item | Needle valve |
| Valve Type | Manual isolation and throttling |
| Form Factor | Straight body hard seat |
| Media Type | Potable water |
| Operator Type | Single handle |
| Body Material | 316L stainless steel |
| Inlet Port | 1/4in male NPT |
| Outlet Port | 1/4in female NPT |
| Minimum Temperature | 10,000 psi @ -67 °F |
| Maximum Temperature | 4,000 psi @ 400 °F |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |
| Other | NSF Listing |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/76250398.pdf>
See store item page for other formats.