

76920B Cut Sheet



Halex fitting, liquid-tight, nylon, 90-degree, 2in trade size, compression conduit connection, insulation, gray. Package of 2. For use with NM-Type B electrical conduit. Sealing washer and locknut included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/76920B>

Technical Specifications

Brand	Halex
Item	Fitting
Liquid-tight	Yes
Fitting Type	90-degree
Material	Nylon
Trade Size	2in
Conduit Connection Method	Compression
Box Connection Type	2in male NPT
Insulation	Yes

Color	Gray
Knockout Size	2in
Liquid-tight Non-metallic Conduit Type B (NM) Trade Size	2in
Quantity per Pack	2
For Use With	NM-Type B electrical conduit
Includes	Sealing washer and locknut
Applicable Standards	UL 514B Listed

Agency Approvals

UL Listed File #	E30248
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement