


# 7700-12341-U040300 Cut Sheet



Murrelektronik connection cable, M12 90-degree female A-coded to pigtail, 4-pole, 250 VAC/VDC, 4A, 22 AWG, TPE jacket, yellow, unshielded, 9.8ft/3m cable length, IP65 IP66K IP67, sensor & signal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7700-12341-U040300>

## Technical Specifications

Brand	Murrelektronik
Item	Cable
Cable Type	Connection
Connection 1	M12 90-degree female with female threads A-coded
Connection 2	Pigtail
Number of Poles	4
Voltage Rating	250 VAC/VDC
Amperage Rating	4A

Conductor Size	22 AWG
Jacket Material	TPE
Jacket Color	Yellow
Shield Type	Unshielded
Cable Length	9.8ft/3m
IP Rating	IP65 IP66K IP67
Application	Sensor & signal

## Agency Approvals

UL Listed File #	E325311
UL Recognized File #	n/a
CE	<a href="#">View CE declarations</a>
CSA File #	n/a
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/7700-12341-U040300.pdf>  
See store item page for other formats.