

7700-44711-S7V0300 Cut Sheet



Murrelektronik Cat5e Ethernet connection cable, M12 axial male D-coded to RJ45 axial male, 4-pole, 60 VDC, 1.5A, 22 AWG, TPE jacket, green, overall aluminum foil and tinned copper braid, 9.8ft/3m cable length, IP67 (M12) IP20 (RJ45), data.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7700-44711-S7V0300>

Technical Specifications

| | |
|------------------------|--|
| Brand | Murrelektronik |
| Item | Cable |
| Cable Type | Cat5e Ethernet connection |
| Connection 1 | M12 axial male with male threads D-coded |
| Connection 2 | RJ45 axial male |
| Number of Poles | 4 |
| Voltage Rating | 60 VDC |
| Amperage Rating | 1.5A |
| Conductor Size | 22 AWG |

| | |
|-------------------------------|---|
| Jacket Material | TPE |
| Jacket Color | Green |
| Shield Type | Overall aluminum foil and tinned copper braid |
| Cable Length | 9.8ft/3m |
| IP Rating | IP67 (M12) IP20 (RJ45) |
| Application | Data |
| For Use With | 10/100 Mbps networks |
| Additional Information | CAT5e ISO/IEC 11801, (Class D bis 100 MBit/s) |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E362618 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | n/a |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/7700-44711-S7V0300.pdf>
See store item page for other formats.