

# 7700-51001-S4X1000 Cut Sheet



Murrelektronik Cat6a Ethernet connection cable, M12 axial male X-coded to M12 axial male X-coded, 8-pole, 60 VDC, 1.5A, 26 AWG, TPE jacket, teal, overall aluminum foil and tinned copper braid, 32.8ft/10m cable length, IP67, data.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7700-51001-S4X1000>

## Technical Specifications

<b>Brand</b>	Murrelektronik
<b>Item</b>	Cable
<b>Cable Type</b>	Cat6a Ethernet connection
<b>Connection 1</b>	M12 axial male with male threads X-coded
<b>Connection 2</b>	M12 axial male with male threads X-coded
<b>Number of Poles</b>	8
<b>Voltage Rating</b>	60 VDC
<b>Amperage Rating</b>	1.5A

<b>Conductor Size</b>	26 AWG
<b>Jacket Material</b>	TPE
<b>Jacket Color</b>	Teal
<b>Shield Type</b>	Overall aluminum foil and tinned copper braid
<b>Cable Length</b>	32.8ft/10m
<b>IP Rating</b>	IP67
<b>Application</b>	Data
<b>Additional Information</b>	CAT6A, ISO/IEC 11801 (Class Ea bis 10 GBit/s)

## Agency Approvals

<b>UL Listed File #</b>	E325311
<b>UL Recognized File #</b>	n/a
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	n/a
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/7700-51001-S4X1000.pdf>  
See store item page for other formats.