

7700-51551-S4X0050 Cut Sheet



Murrelektronik Cat6a Ethernet bulkhead connector, M12 axial female X-coded 8-pin to RJ45 axial male 8-pin, shielded, 26 AWG, 1.6ft/0.5m cable length, HDPE conductor insulation material, IP67 (M12) IP20 (RJ45).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7700-51551-S4X0050>

Technical Specifications

Brand	Murrelektronik
Item	Connector
Form Factor	Bulkhead
Connector Standard	Cat6a Ethernet
Field-Wireable	No
Connection 1	M12 axial female with female threads X-coded 8-pin
Connection 2	RJ45 axial male 8-pin
Shielded	Yes
Cable Length	1.6ft/0.5m
Conductor Size	26 AWG
Conductor Insulation Material	HDPE
IP Rating	IP67 (M12) IP20 (RJ45)
Additional Information	CAT6A, ISO/IEC 11801, (Class Ea bis 10 GBit/s)

Agency Approvals

UL Listed File #	E325311
UL Recognized File #	n/a
CE	View CE declarations
CSA File #	n/a
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/7700-51551-S4X0050.pdf>
See store item page for other formats.