

7700-A4A01-U0C0100 Cut Sheet



Murrelektronik connection cable, 7/8in - 16 UN2 axial male with male threads to 7/8in - 16 UN2 axial female with female threads, 4-pole, 600 VAC/VDC, 9A, 16 AWG, TPE jacket, yellow, unshielded, 3.2ft/1m cable length, IP68, power.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7700-A4A01-U0C0100>

Technical Specifications

Brand	Murrelektronik
Item	Cable
Cable Type	Connection
Connection 1	7/8in - 16 UN2 axial male with male threads
Connection 2	7/8in - 16 UN2 axial female with female threads
Number of Poles	4
Voltage Rating	600 VAC/VDC
Amperage Rating	9A

Conductor Size	16 AWG
Jacket Material	TPE
Jacket Color	Yellow
Shield Type	Unshielded
Cable Length	3.2ft/1m
IP Rating	IP68
Application	Power

Agency Approvals

UL Listed File #	E325311
UL Recognized File #	NA
CE	None
CSA File #	n/a
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/7700-A4A01-U0C0100.pdf>
See store item page for other formats.