

# 7700-A4A31-U0C0300 Cut Sheet



Murrelektronik connection cable, 7/8in - 16 UN2 90-degree male with male threads to 7/8in - 16 UN2 90-degree female with female threads, 4-pole, 600 VAC/VDC, 9A, 16 AWG, TPE jacket, yellow, unshielded, 9.8ft/3m cable length, IP68, power.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7700-A4A31-U0C0300>

## Technical Specifications

Brand	Murrelektronik
Item	Cable
Cable Type	Connection
Connection 1	7/8in - 16 UN2 90-degree male with male threads
Connection 2	7/8in - 16 UN2 90-degree female with female threads
Number of Poles	4
Voltage Rating	600 VAC/VDC
Amperage Rating	9A

Conductor Size	16 AWG
Jacket Material	TPE
Jacket Color	Yellow
Shield Type	Unshielded
Cable Length	9.8ft/3m
IP Rating	IP68
Application	Power

## Agency Approvals

UL Listed File #	E325311
UL Recognized File #	NA
CE	None
CSA File #	n/a
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/7700-A4A31-U0C0300.pdf>  
See store item page for other formats.