


# 7700-P4221-U0D1000 Cut Sheet



Murrelektronik power cable, M12 axial female L-coded to pigtail, 5-pole, 63 VDC, 12A, 16 AWG, TPE jacket, yellow, 32.8ft/10m cable length, IP65 IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7700-P4221-U0D1000>

## Technical Specifications

<b>Brand</b>	Murrelektronik
<b>Item</b>	Cable
<b>Cable Type</b>	Power
<b>Connection 1</b>	M12 axial female L-coded
<b>Connection 2</b>	Pigtail
<b>Number of Poles</b>	5
<b>Voltage Rating</b>	63 VDC
<b>Amperage Rating</b>	12A
<b>Conductor Size</b>	16 AWG
<b>Jacket Material</b>	TPE
<b>Jacket Color</b>	Yellow
<b>Cable Length</b>	32.8ft/10m
<b>IP Rating</b>	IP65 IP67

## Agency Approvals

<b>UL Listed File #</b>	E492831
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/7700-P4221-U0D1000.pdf>  
See store item page for other formats.