

7700-P4241-U0P0750 Cut Sheet



Murrelektronik power cable, M12 axial male L-coded to M12 axial female L-coded, 5-pole, 63 VDC, 16A, 14 AWG, TPE jacket, yellow, 24.6ft/7.5m cable length, IP65 IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7700-P4241-U0P0750>

Technical Specifications

| | |
|------------------------|--------------------------|
| Brand | Murrelektronik |
| Item | Cable |
| Cable Type | Power |
| Connection 1 | M12 axial male L-coded |
| Connection 2 | M12 axial female L-coded |
| Number of Poles | 5 |
| Voltage Rating | 63 VDC |
| Amperage Rating | 16A |
| Conductor Size | 14 AWG |
| Jacket Material | TPE |
| Jacket Color | Yellow |
| Cable Length | 24.6ft/7.5m |
| IP Rating | IP65 IP67 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E492831 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/7700-P4241-U0P0750.pdf>
See store item page for other formats.