

7803125 Cut Sheet



KNIPEX precision diagonal cutters, 5.0in (127mm) overall length, flush cutting edges, multi-component soft grip.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7803125>

Technical Specifications

Brand	KNIPEX
Item	Cutters
Pliers Type	Precision diagonal
Overall Length	5.0in (127mm)
Insulated	No
Cutting	Flush cutting edges
Capacity	1/64–1/16in soft wire
Handle Type	Multi-component soft grip
Application	Wire cutting
Material	Inox stainless steel
Applicable Standards	DIN ISO 9654

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document