

7861125SBA Cut Sheet



KNIPEX precision diagonal cutters, 5.0in (127mm) overall length, flush cutting edges, multi-component soft grip handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7861125SBA>

Technical Specifications

Brand	KNIPEX
Item	Cutters
Pliers Type	Precision diagonal
Overall Length	5.0in (127mm)
Insulated	No
Cutting	Flush cutting edges
Capacity	1/64–1/16in soft wire
Handle Type	Multi-component soft grip handle
Application	Wire cutting
Material	Special tool steel, multi-stage oil-hardened
Applicable Standards	DIN ISO 9654

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement