

# 787-1662-004-1000 Cut Sheet



WAGO electronic circuit protector, current-limiting, 3.8A, 24 VDC, 2 independent channel(s), NEC Class 2, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/787-1662-004-1000>

## Technical Specifications

Brand	WAGO
Item	Circuit protector
Circuit Breaker Type	Compact
Circuit Type	Supplementary
Current-Limiting	Yes
Amperage Rating	3.8A
Input voltage range	18-30 VDC
Output Voltage Range	18-30 VDC
Channels	2 independent
Trip Type	Electronic
Reset	Remote or local
NEC Class 2	Yes
Mounting	35mm DIN rail
Connection	Push-in cage clamp

## Agency Approvals

UL Listed File #	E255817
UL Recognized File #	E363438
UL Hazardous File #	NONE
CE	<a href="#">View CE declarations</a>
CSA File #	NONE
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/787-1662-004-1000.pdf>  
See store item page for other formats.