

787-1664-006-1000 Cut Sheet



WAGO electronic circuit protector, current-limiting, adjustable 0.5-6A, 24 VDC, 4 independent channel(s), 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/787-1664-006-1000>

Technical Specifications

Brand	WAGO
Item	Circuit protector
Circuit Breaker Type	Compact
Circuit Type	Supplementary
Current-Limiting	Yes
Amperage Rating	Adjustable 0.5-6A
Input voltage range	18-30 VDC
Output Voltage Range	18-30 VDC
Channels	4 independent
Trip Type	Electronic
Reset	Remote or local
Mounting	35mm DIN rail
Connection	Push-in cage clamp

Agency Approvals

UL Listed File #	E255817
UL Recognized File #	E363438
UL Hazardous File #	NONE
CE	View CE declarations
CSA File #	NONE
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	DNV GL Approval