

# 787-1668 Cut Sheet



WAGO electronic circuit protector, adjustable 2-10A, 24 VDC, 8 independent channel(s), 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/787-1668>

## Technical Specifications

<b>Brand</b>	WAGO
<b>Item</b>	Circuit protector
<b>Circuit Breaker Type</b>	Compact
<b>Circuit Type</b>	Supplementary
<b>Amperage Rating</b>	Adjustable 2-10A
<b>Input voltage range</b>	18-30 VDC
<b>Output Voltage Range</b>	18-30 VDC
<b>Channels</b>	8 independent
<b>Trip Type</b>	Electronic
<b>Reset</b>	Remote or local
<b>Mounting</b>	35mm DIN rail
<b>Connection</b>	Push-in cage clamp

## Agency Approvals

<b>UL Listed File #</b>	E255817
<b>UL Recognized File #</b>	E363438
<b>UL Hazardous File #</b>	NONE
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	NONE
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">DNV GL Approval</a>