



Exact 12 passive distribution block, 8 ports, 5-pin M12 A-coded sockets, 5-wire, 24 VDC, 4A, power and PNP LED indicator(s), plug-in screw terminals, IP67 and IP65. Terminal blocks and marking tags included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/8000-88550-0000000>

Technical Specifications

Brand	Exact 12
Item	Passive distribution block
Number of Ports	8
Socket Type	5-pin M12 A-coded
Wires Per Socket	5-wire
Socket Current	4A
I/O Per Socket	2

Voltage Rating	24 VDC
Number Of Commons	1
Load Current	8A/common
Indicator	Power and PNP LED
Connection	Plug-in screw terminals
IP Rating	IP67 and IP65
Includes	Terminal blocks and marking tags

Agency Approvals

UL Listed File #	E325311
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	View CE declarations
CSA File #	N/A
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/8000-88550-0000000.pdf>
See store item page for other formats.