

804 Cut Sheet



CHANNELLOCK adjustable wrench, 0-1/2in, 4.5in (114mm) overall length, 4-thread knurl adjuster and laser engraved measurement scales.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/804>

Technical Specifications

Brand	CHANNELLOCK
Item	Wrench
Wrench Type	Adjustable
Fastening Size	0-1/2in
Ratcheting	No
Insulated	No
Jaw Thickness	0.37in (9.5mm)
Overall Length	4.5in (114mm)
Material	Chrome Vanadium steel
Wrench Features	4-thread knurl adjuster and laser engraved measurement scales

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document