

808W Cut Sheet



CHANNELLOCK adjustable wrench, 0-1 1/16in, 8.0in (203mm) overall length, extra wide jaws, 4-thread knurl adjuster and laser engraved measurement scales.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/808W>

Technical Specifications

Brand	CHANNELLOCK
Item	Wrench
Wrench Type	Adjustable
Fastening Size	0-1 1/16in
Ratcheting	No
Insulated	No
Jaw Thickness	0.55in (14.0mm)
Overall Length	8.0in (203mm)
Material	Chrome Vanadium steel
Tool Features	Extra wide jaws, 4-thread knurl adjuster and laser engraved measurement scales

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document