

836052 Cut Sheet



Murrplastik KW fitting, 90-degree, threaded/compression, M16/P11 tubing size, black. Package of 5. For use with EW-PAB and EW-PRF series flexible corrugated solid tubing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/836052>

Technical Specifications

Brand	Murrplastik
Series	KW
Item	Fitting
Liquid-tight	No
Fitting Type	90-degree
Tubing Connection Method	Threaded/compression
Material	Modified polyamide 6
Tubing Size	M16/P11
Box Connection Type	M20 x 1.5 mm

Color	Black
Quantity per Pack	5
IP Rating	IP65
Flammability	UL 94 V-0
Operating Temperature	-40 to +230 °F (-40 to +110 °C)
UV Resistant	No
For Use With	EW-PAB and EW-PRF series flexible corrugated solid tubing
Applicable Standards	UL 1696

Agency Approvals

UL Recognized File #	E148958
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/836052.pdf>
See store item page for other formats.