

# 838116 Cut Sheet



Murrplastik EW-PAB solid flexible corrugated tubing, modified polyamide 6, M20/P16 tubing size, black, 32.8ft/10m coil length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/838116>

## Technical Specifications

<b>Brand</b>	Murrplastik
<b>Series</b>	EW-PAB
<b>Item</b>	Corrugated tubing
<b>Tubing Type</b>	Solid
<b>Flexibility</b>	Flexible
<b>Liquid-tight</b>	No
<b>Material</b>	Modified polyamide 6
<b>Tubing Size</b>	M20/P16
<b>Color</b>	Black

<b>Coil Length</b>	32.8ft/10m
<b>IP Rating</b>	IP54 IP65
<b>Flammability</b>	UL 94 V-0
<b>Operating Temperature</b>	-49 to +248 °F (-45 to +120 °C)
<b>UV Resistant</b>	Yes
<b>Flexural Fatigue</b>	>11000 Cycles per IEC EN 61386
<b>Crush Resistance</b>	>74 lbf (330 N) 50x50mm per IEC EN 61386 M25/P21 @23C
<b>Applicable Standards</b>	UL 1696

## Agency Approvals

<b>UL Recognized File #</b>	E148958
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/838116.pdf>  
See store item page for other formats.