

# 838150 Cut Sheet



Murrplastik KW fitting, 90-degree, threaded/compression, M20/P16 tubing size, black. Package of 5. For use with EW-PAB and EW-PRF series flexible corrugated solid tubing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/838150>

## Technical Specifications

<b>Brand</b>	Murrplastik
<b>Series</b>	KW
<b>Item</b>	Fitting
<b>Liquid-tight</b>	No
<b>Fitting Type</b>	90-degree
<b>Tubing Connection Method</b>	Threaded/compression
<b>Material</b>	Modified polyamide 6
<b>Tubing Size</b>	M20/P16
<b>Box Connection Type</b>	1/2in male NPT

<b>Color</b>	Black
<b>Quantity per Pack</b>	5
<b>IP Rating</b>	IP65
<b>Flammability</b>	UL 94 V-0
<b>Operating Temperature</b>	-40 to +230 °F (-40 to +110 °C)
<b>UV Resistant</b>	No
<b>For Use With</b>	EW-PAB and EW-PRF series flexible corrugated solid tubing
<b>Applicable Standards</b>	UL 1696

## Agency Approvals

<b>UL Recognized File #</b>	E148958
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/838150.pdf>  
See store item page for other formats.