

838152 Cut Sheet



Murrplastik KW fitting, 90-degree, threaded/compression, M25/P21 tubing size, black. Package of 5. For use with EW-PAB and EW-PRF series flexible corrugated solid tubing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/838152>

Technical Specifications

| | |
|--------------------------|----------------------|
| Brand | Murrplastik |
| Series | KW |
| Item | Fitting |
| Liquid-tight | No |
| Fitting Type | 90-degree |
| Tubing Connection Method | Threaded/compression |
| Material | Modified polyamide 6 |
| Tubing Size | M25/P21 |
| Box Connection Type | 3/4in male NPT |

| | |
|-----------------------|---|
| Color | Black |
| Quantity per Pack | 5 |
| IP Rating | IP65 |
| Flammability | UL 94 V-0 |
| Operating Temperature | -40 to +230 °F (-40 to +110 °C) |
| UV Resistant | No |
| For Use With | EW-PAB and EW-PRF series flexible corrugated solid tubing |
| Applicable Standards | UL 1696 |

Agency Approvals

| | |
|----------------------|---|
| UL Recognized File # | E148958 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/838152.pdf>
See store item page for other formats.