

# 838351 Cut Sheet



Murrplastik EH fitting, straight, threaded/compression, M16/P11 tubing size, black. Package of 5. For use with EW-PAB and EW-PRF series flexible corrugated solid tubing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/838351>

## Technical Specifications

|                          |                      |
|--------------------------|----------------------|
| Brand                    | Murrplastik          |
| Series                   | EH                   |
| Item                     | Fitting              |
| Liquid-tight             | No                   |
| Fitting Type             | Straight             |
| Tubing Connection Method | Threaded/compression |
| Material                 | Modified polyamide 6 |
| Tubing Size              | M16/P11              |
| Box Connection Type      | 3/8in male NPT       |

|                       |   |
|-----------------------|---|
| Color                 | Black   |
| Quantity per Pack     | 5   |
| IP Rating             | IP65  |
| Flammability          | UL 94 V-0   |
| Operating Temperature | -40 to +230 °F (-40 to +110 °C)                           |
| UV Resistant          | No  |
| For Use With          | EW-PAB and EW-PRF series flexible corrugated solid tubing |
| Applicable Standards  | UL 1696   |

## Agency Approvals

|                      |   |
|----------------------|---|
| UL Recognized File # | E148958   |
| RoHS Status          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH             | <a href="#">View EU REACH document</a>                              |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/838351.pdf>  
See store item page for other formats.