

838450 Cut Sheet



Murrplastik UH-S clamp, M20/P16 tubing size, black. Package of 5. For use with EW-PAB and EW-PRF series flexible corrugated solid tubing and EWT-PA series flexible corrugated split tubing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/838450>

Technical Specifications

Brand	Murrplastik
Series	UH-S
Item	Clamp
Liquid-tight	No
Material	Modified polyamide 6
Tubing Size	M20/P16
Color	Black
Quantity per Pack	5
Flammability	UL 94 V-0 and 5VA
Operating Temperature	-40 to +230 °F (-40 to +110 °C)
UV Resistant	Yes
For Use With	EW-PAB and EW-PRF series flexible corrugated solid tubing and EWT-PA series flexible corrugated split tubing
Applicable Standards	UL 1696

Agency Approvals

UL Recognized File #	E148958
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/838450.pdf>
See store item page for other formats.