

84900077 Cut Sheet



WERMA buzzer element, 80 dB at 1m, 21 kHz tone frequency, continuous/pulse tone(s), 115 VAC/VDC, ABS/polycarbonate housing, black, IP54. For use with WERMA 50mm stack light elements.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/84900077>

Technical Specifications

Brand	WERMA
Item	Buzzer element
Loudness Decibel	80 dB at 1m
Tone Frequency	21 kHz
Tone Type	Continuous/pulse
Touch to Acknowledge	No
Number of Alarms	2
Voltage Rating	115 VAC/VDC
Housing Material	ABS/polycarbonate
Color	Black
IP Rating	IP54
For Use With	WERMA 50mm stack light elements

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/84900077.pdf>
See store item page for other formats.