


859-805 Cut Sheet



WAGO DC to DC converter, 10-30 VDC input, 12 VDC output, 0.5A, 6W, plastic housing, 35mm DIN rail mount, cage clamp.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/859-805>

Technical Specifications

Brand	WAGO
Item	DC to DC converter
Input voltage range	10-30 VDC
Output Voltage Range	12 VDC
Load Current	0.5A
Output Power	6W
Housing Material	Plastic
Encapsulated	No
Mounting	35mm DIN rail
Terminal Block Type	Cage clamp
Removable	No

Agency Approvals

UL Listed File #	E175199
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document