

8603180SBA Cut Sheet



KNIPEX adjustable push button pliers wrench, 7.3in (184mm) overall length, non-slip plastic coated handles, smooth gripping surface, push button adjustment and parallel jaws.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/8603180SBA>

Technical Specifications

Brand	KNIPEX
Item	Pliers wrench
Pliers Type	Adjustable push button
Overall Length	7.3in (184mm)
Insulated	No
Capacity	1-1/2in hex
Handle Type	Non-slip plastic coated handles

Application	Fastening
Material	Chrome vanadium electric steel, forged, oil-hardened
Tool Features	Smooth gripping surface, push button adjustment and parallel jaws
Additional Information	15 adjustment positions - replaces full set of inch and metric open ended wrenches up to 1.5in

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement