

8603250SBA Cut Sheet

KNIPEX adjustable push button pliers wrench, 10.0in (254mm) overall length, non-slip plastic coated handles, smooth gripping surface, push button adjustment and parallel jaws.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/8603250SBA>

Technical Specifications

Brand	KNIPEX
Item	Pliers wrench
Pliers Type	Adjustable push button
Overall Length	10.0in (254mm)
Insulated	No
Capacity	2in hex
Handle Type	Non-slip plastic coated handles
Application	Fastening
Material	Chrome vanadium electric steel, forged, oil-hardened
Tool Features	Smooth gripping surface, push button adjustment and parallel jaws
Additional Information	19 adjustment positions - replaces full set of inch and metric open ended wrenches up to 2in

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document