

# 8603300SBA Cut Sheet

KNIPEX adjustable push button pliers wrench, 12.0in (305mm) overall length, non-slip plastic coated handles, smooth gripping surface, push button adjustment and parallel jaws.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/8603300SBA>

---

## Technical Specifications

<b>Brand</b>	KNIPEX
<b>Item</b>	Pliers wrench
<b>Pliers Type</b>	Adjustable push button
<b>Overall Length</b>	12.0in (305mm)
<b>Insulated</b>	No
<b>Capacity</b>	2-1/2in hex
<b>Handle Type</b>	Non-slip plastic coated handles
<b>Application</b>	Fastening
<b>Material</b>	Chrome vanadium electric steel, forged, oil-hardened
<b>Tool Features</b>	Smooth gripping surface, push button adjustment and parallel jaws
<b>Additional Information</b>	24 adjustment positions - replaces full set of inch and metric open ended wrenches up to 2.5in

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>