

8604100SBA Cut Sheet



KNIPEX adjustable pliers wrench, 4.0in (102mm) overall length, texturized chrome-plated steel handles, finger pinch guard, smooth gripping surface, parallel jaws and extra small profile.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/8604100SBA>

Technical Specifications

Brand	KNIPEX
Item	Pliers wrench
Pliers Type	Adjustable
Overall Length	4.0in (102mm)
Insulated	No
Capacity	3/4in hex
Handle Type	Texturized chrome-plated steel handles
Application	Fastening

Material	Chrome vanadium electric steel, forged, oil-hardened
Tool Features	Finger pinch guard, smooth gripping surface, parallel jaws and extra small profile
Additional Information	10 adjustment positions -replaces inch and metric open ended wrenches up to 0.75in capacity. Pocket sized for EDC

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement