

8700100SBA Cut Sheet



KNIPEX Cobra adjustable pliers, 4.0in (102mm) overall length, texturized gray atramentized steel handles, finger pinch guard, serrated gripping surface and extra small profile.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/8700100SBA>

Technical Specifications

Brand	KNIPEX
Series	Cobra
Item	Pliers
Pliers Type	Adjustable
Overall Length	4.0in (102mm)
Insulated	No
Capacity	1in round or 1-1/16in hex
Handle Type	Texturized gray atramentized steel handles

Application	Gripping
Material	Chrome vanadium electric steel, forged, oil-hardened
Tool Features	Finger pinch guard, serrated gripping surface and extra small profile
Additional Information	11 adjustment positions. One-handed quick adjustment up to 1in capacity. Pocket sized for EDC

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement