

8801250SBA Cut Sheet

KNIPEX Alligator adjustable pliers, 10.0in (254mm) overall length, non-slip plastic coated handles, finger pinch guard and serrated gripping surface.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/8801250SBA>

Technical Specifications

Brand	KNIPEX
Series	Alligator
Item	Pliers
Pliers Type	Adjustable
Overall Length	10.0in (254mm)
Insulated	No
Capacity	2in round or 1-13/16in hex
Handle Type	Non-slip plastic coated handles

Application	Gripping
Material	Chrome vanadium electric steel, forged, oil-hardened
Applicable Standards	DIN ISO 8976
Tool Features	Finger pinch guard and serrated gripping surface
Additional Information	9 adjustment positions for 30% more gripping capacity

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document